

Clamping screw sets



Execution:

- Tempered
- Strength class 8 or 10
- Different clamping heights can be set as required using extension nuts and studs (extension studs).
- Widths across flats are in accordance with ISO standard (DIN ISO 272)

Delivery:

In a sturdy, high-quality wooden box with removable hinged lid.



| | |
|--|---|
| Art. no. | 26209 160 |
| Brand | AMF |
| Manufacturer Part Number | 83014 |
| Suitable for groove width | 16 mm |
| Thread dimension | M14 |
| Number of DIN 787 T-slot screws | 2 x M14 x 63 mm, 4 x M14 x 100 mm |
| Number of DIN 6379 stud bolts (extension pin) | 4 x M14 x 63 mm, 4 x M14 x 100 mm, 4 x M14 x 160 mm, 4 x M14 x 250 mm |
| Number of DIN 508 slots | 4 PCS |
| Number of DIN 6330 B high nuts | 4 PCS |
| Number of extension nuts | 4 PCS |
| Wooden box length | 317 mm |
| Wooden box width | 239 mm |
| Wooden box height | 44 mm |
| Gross Weight | 5.200 kg |
| Product Group | 260 |

EAN

4020772083014