


Insaver LED 75 - Round

Insaver 75 LED RS NW DB WH
3097101



Product features

- A round (4000K) neutral white LED downlight with phase dimmable driver, finished in a white finish , Colour rendering index Ra >80, , Class II, Protection rating IP65/IK02



PRODUCT OVERVIEW

Product name	Insaver 75 LED RS NW DB WH
Technology	LED
Housing	Aluminium
Mount	Ceiling recessed mounting
Environment	External (remote)
General application	Hospitality, Residential & Consumer
ETIM Class	EC001744
E-number FI	4271172
E-number SE	7467429
Warranty	3 years
Fixture luminous flux (lm)	1200
Luminaire efficacy (lm/W)	75
Colour temperature (K)	4000
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM5
Beam Angle (°)	55
Photobiological Risk Group	RG1
Total power consumption (W)	16
Electrical protection	Class II
Control gear type	Other
Housing colour	White
IP rating	IP65/20
IK rating	IK02
Product EAN number	8711971971016

DATA TABLE

General data

Product name	Insaver 75 LED RS NW DB WH
Technology	LED
Housing	Aluminium
Mount	Ceiling recessed mounting
Environment	External (remote)

Insafer LED 75 - Round

Insafer 75 LED RS NW DB WH
3097101

General application	Hospitality, Residential & Consumer
ETIM Class	EC001744
E-number FI	4271172
E-number SE	7467429
Warranty	3 years

Optical data

Fixture luminous flux (lm)	1200
Luminaire efficacy (lm/W)	75
Colour temperature (K)	4000
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM5
Adjustable chromaticity	N
Beam Angle (°)	55
Distribution type	Symmetric
Photobiological Risk Group	RG1

Electrical data

Total power consumption (W)	16
Mains voltage (V)	220-240V
Electrical protection	Class II
Control gear type	Other
Transformer required	Yes
Drive current (mA)	350

Physical data

Housing colour	White
IP rating	IP65/20
IK rating	IK02
Diffuser finish	Transparent
Diffuser material	Glass
Nominal Product Height (mm)	65
Nominal Product Diameter (mm)	90
Cutout Dimensions (W x L in mm or Diameter in mm)	75
Weight (kg)	0.441


Packaging

Single packaging type	Carton
Product EAN number	8711971971016
Packaging single length / height (cm)	15.9
Packaging single width (cm)	8.5
Packaging single depth (cm)	14.9
DUN14 (outer)	18711971971013
Units per outer package	20
Packaging outer length / height (cm)	46.4
Packaging outer width (cm)	32.2
Packaging outer depth (cm)	34.6

Insaver LED 75 - Round

Insaver 75 LED RS NW DB WH
3097101

PHOTOMETRY



TECHNICAL DRAWINGS

