





Hauptschalter-Not-Aus, für Einbau 4-Lochbefestigung, absperrrbar IP66

		max. Schlösser	AC21 690V	AC23 3x400V	Schild	Typ	VPE Stk.	Gewicht kg/Stk.
3-polig, Sperrvorrichtung SV1 								
			20A	7,5kW	48 □ ¹⁾	LTS20 EHN1 A3	1	0,15
			25A	10kW	48 □ ¹⁾	LTS25 EHN1 A3	1	0,15
			32A	12,5kW	48 □ ¹⁾	LTS32 EHN1 A3	1	0,15
			40A	16kW	48 □ ¹⁾	LTS40 EHN1 A3	1	0,15
			63A	22kW	48 □ ¹⁾	LTS63 EHN1 A3	1	0,17
			80A	22kW	48 □ ¹⁾	LTS80 EHN1 A3	1	0,17
4-polig, Sperrvorrichtung SV1 								
			20A	7,5kW	48 □ ¹⁾	LTS20 EHN1 A4	1	0,19
			25A	10kW	48 □ ¹⁾	LTS25 EHN1 A4	1	0,19
			32A	12,5kW	48 □ ¹⁾	LTS32 EHN1 A4	1	0,19
			40A	16kW	48 □ ¹⁾	LTS40 EHN1 A4	1	0,19
			63A	22kW	48 □ ¹⁾	LTS63 EHN1 A4	1	0,21
			80A	22kW	48 □ ¹⁾	LTS80 EHN1 A4	1	0,21
6-polig , 8-polig						auf Anfrage		
3-polig, Sperrvorrichtung SV4(34) 								
			20A	7,5kW	64 □ ²⁾	LTS20 EHN4 A3	1	0,17
			25A	10kW	64 □ ²⁾	LTS25 EHN4 A3	1	0,17
			32A	12,5kW	64 □ ²⁾	LTS32 EHN4 A3	1	0,17
			40A	16kW	64 □ ²⁾	LTS40 EHN4 A3	1	0,17
			63A	22kW	64 □ ²⁾	LTS63 EHN4 A3	1	0,19
			80A	22kW	64 □ ²⁾	LTS80 EHN4 A3	1	0,19
			85A	30kW	64 □ ²⁾	LTS85 EHN4 A3	1	0,39
			100A	37kW	64 □ ²⁾	LTS100 EHN4 A3	1	0,39
			125A	45kW	64 □ ²⁾	LTS125 EHN4 A3	1	0,39
	160A	55kW	88 □	LT160 EHN34 T300	1	1,16		
4-polig, Sperrvorrichtung SV4(34) 								
			20A	7,5kW	64 □ ²⁾	LTS20 EHN4 A4	1	0,20
			25A	10kW	64 □ ²⁾	LTS25 EHN4 A4	1	0,20
			32A	12,5kW	64 □ ²⁾	LTS32 EHN4 A4	1	0,20
			40A	16kW	64 □ ²⁾	LTS40 EHN4 A4	1	0,20
			63A	22kW	64 □ ²⁾	LTS63 EHN4 A4	1	0,23
			80A	22kW	64 □ ²⁾	LTS80 EHN4 A4	1	0,23
			85A	30kW	64 □ ²⁾	LTS85 EHN4 A4	1	0,44
			100A	37kW	64 □ ²⁾	LTS100 EHN4 A4	1	0,44
			125A	45kW	64 □ ²⁾	LTS125 EHN4 A4	1	0,44
	160A	55kW	88 □	LT160 EHN34 T400	1	1,55		

Zusatzmodule siehe Seite 6

- 1) Auf Anfrage auch in Schildgröße 64 □ erhältlich, Typenzusatz **64** z. B: LTS32 EHN1**64** A3
- 2) Auf Anfrage auch in Schildgröße 88 □ erhältlich, Typenzusatz **88** z. B: LTS32 EHN1**88** A3