

Model No.	BN 2353904	BN 2353905	BN 2353907	BN 2353906
Button Type	Flat	Convex	Flat	Convex
Case Material	Stainless Steel			
Terminations	Solder Tags			
LED Voltage	DC 9~30V			
Switch Type	SPDT			
Contact Rating	DC 24V 2A / AC 24V 1A			
Initial Contact Resistance	<50mΩ			
Operation Temperature	-20°C~70°C			
Operation Life	1x10 ⁵ cycles			
Mounting Diameter	19mm			
Travel	1.5mm			
LED Colour	—		xx = Red/Green/Blue/Yellow/White	
Sealing (Front Panel Only)	Protection Classification IP66			

