

Product information

97 52 38

KNIPEX PreciForce® Crimping Pliers


- Consistently high crimping quality thanks to precision dies and ratchet mechanism (unlockable)
- Tools have been set precisely (calibrated) in the factory
- Optimum transmission of force thanks to toggle lever for fatigue-reduced operation
- Good handling thanks to favourable handle position, low weight, compact design and ergonomically shaped handles
- Special quality chrome vanadium electric steel, oil-hardened



General

Article No.	97 52 38
EAN	4003773051909
Pliers	burnished
Handles	with multi-component grips
Weight	493 g
Dimensions	220 x 58 x 21 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable

Technical details



Application	insulated and non-insulated wire ferrules
Capacity in square millimetres	0.25 — 6.0 mm ²
Number of crimping positions	5
AWG	24 — 10

technical change and errors excepted