

Pneumatic ratchet screwdriver MDR 2100

**MANNESMANN
DEMAG**

Application:

For use in confined spaces

Execution:

- Thermally insulated soft handle
- Exhaust air duct can be rotated 360°
- With speed control



Art. no.	75061 200
Brand	MANNESMANN DEMAG
Manufacturer Part Number	82400102
Model	MDR 2100
Suitable for screw	M10
Max. tightening torque	55 Nm
Max. idle speed	220 rpm
Air consumption	4.7 l/s
Tool holding device	1/4-inch external square
Connection thread	NPT 1/4 inch
Inner hose diameter	8 mm
Sound-pressure level	82 dB
Valve design	Lever valve
Length	200 mm
Weight	0.6 kg
With right/left-hand rotation	Yes
Gross Weight	0.641 kg
Product Group	7AA

EAN

4251757302701