




Heavy-Duty Cable Ties

Heavy-duty design offers 120 and 175 lbs of tensile strength.

- Patented DoubleLock® design (on 120 lb) ensures 50% greater tensile strength.
- Ultraviolet black (UVB) ties resist harmful light rays – primarily for outdoor use.



Length A	Part #	Pkg Qty	DoubleLock®	Tensile Strength	Width B	Thickness C	Bundle Dia. Max.	UL	Color
8"	46-408	100/bag	✓	120 lb	0.25"	.072"	2"	UR	Natural
	46-408UVB	100/bag	✓	120 lb	0.25"	.072"	2"	UR	Black
12"	46-412	100/bag	✓	120 lb	0.25"	.072"	3"	UR	Natural
	46-412UVB	100/bag	✓	120 lb	0.25"	.072"	3"	UR	Black
15"	45-515	10/bag	✓	120 lb	0.25"	.072"	4"	UR	Natural
	46-415	50/bag	✓	120 lb	0.25"	.072"	4"	UR	Natural
	45-515UVB	10/bag	✓	120 lb	0.25"	.072"	4"	UR	Black
	46-415UVB	50/bag	✓	120 lb	0.25"	.072"	4"	UR	Black
17"	45-518N	10/bag	—	175 lb	0.35"	.07"	4.90"	UR	Natural
	46-418	50/bag	—	175 lb	0.35"	.07"	4.90"	UR	Natural
	45-518UVBN	10/bag	—	175 lb	0.35"	.07"	4.90"	UR	Black
	46-418UVB	50/bag	—	175 lb	0.35"	.07"	4.90"	UR	Black
21"	45-521	10/bag	—	175 lb	0.35"	.07"	5.5"	UR	Natural
	46-421	50/bag	—	175 lb	0.35"	.07"	5.51"	UR	Natural
	45-521UVB	10/bag	—	175 lb	0.35"	.07"	5.51"	UR	Black
	46-421UVB	50/bag	—	175 lb	0.35"	.07"	5.5"	UR	Black
24"	45-524	10/bag	—	175 lb	0.35"	.07"	7"	UR	Natural
	46-424	50/bag	—	175 lb	0.35"	.07"	7"	UR	Natural
	45-524UVB	10/bag	—	175 lb	0.35"	.07"	7"	UR	Black
	46-424UVB	50/bag	—	175 lb	0.35"	.07"	7"	UR	Black
30"	46-330	25/bag	—	175 lb	0.35"	.07"	9"	UR	Natural
	46-330UVB	25/bag	—	175 lb	0.35"	.07"	9"	UR	Black
36"	45-536	10/bag	—	175 lb	0.35"	.07"	10.30"	UR	Natural
	46-436	50/bag	—	175 lb	0.35"	.07"	10.30"	UR	Natural
	45-536UVB	10/bag	—	175 lb	0.35"	.07"	10.30"	UR	Black
	46-436UVB	50/bag	—	175 lb	0.35"	.07"	10.30"	UR	Black
48"	45-548	10/bag	—	175 lb	0.35"	.07"	14.30"	UR	Natural
	46-448	50/bag	—	175 lb	0.35"	.07"	14.30"	UR	Natural
	45-548UVB	10/bag	—	175 lb	0.35"	.07"	14.30"	UR	Black
	46-448UVB	50/bag	—	175 lb	0.35"	.07"	14.30"	UR	Black