

Quick coupling plug KS3-CK-6

Part number: 3478

FESTO



Data sheet

Feature	Value
Nominal width	4.9 mm
Type code	KS3
Operating pressure for entire temperature range	-0.95 bar ... 12 bar
Standard nominal flow rate	378 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-10 °C ... 60 °C
Product weight	21 g
Pneumatic connection 1	CK-6
Note on materials	RoHS-compliant