




ZDO6H05DMSS0000-00STAK190MSS

Connection technology



#### Product characteristics

Splitter box

M23 connector


Free from halogen

Free from silicone

Gold-plated contacts

#### Electrical data

Electrical design	DC
Operating voltage [V]	10...30 DC; "supply class 2" to cULus.
Max. total current load [A]	10
Max. current load per location [A]	4
Environment	
Ambient temperature [°C]	-25...80
Protection	IP 67; (enclosure type 1)
Mechanical data	
Design	6 way
Housing materials	PA
Tightening torque for knurled nut [Nm]	0.8...1.5 *)
Weight [kg]	0.238
Displays / operating elements	
Output status indication LED	12 x yellow
Operation LED	green
Electrical connection	
Connection	M23 connector
Wiring	



**Accessories**

Accessories (included)	2 protective caps; 6 labels
------------------------	-----------------------------

**Remarks**

Remarks	*) Take into account the maximum value of the counterpart!
---------	--

Pack quantity	[piece]	1
---------------	---------	---

**Other data**

Ports	M12
-------	-----

ifm electronic gmbh • Friedrichstraße 1 • 45128 Essen — We reserve the right to make technical alterations without prior notice. — GB — EBC008 — 29.11.2011