

T-slot bolts



Application:

For clamping workpieces on machine tables.

Execution:

- Tempered
- Rolled thread
- Forged
- With milled groove guide
- M8 to M12, strength class 10.9
- M16 to M24, strength class 8.8
- DIN 787



Art. no.	26200 935
Brand	AMF
Manufacturer Part Number	8 1216
DIN	787
Thread dimension	M24
Groove width	24 mm
Length excluding head	100 mm
Outer diameter	23.7 mm
Thread length	70 mm
Length of head	40 mm
Head height	16 mm
Gross Weight	0.822 kg
Product Group	260

EAN

4020772081218