


Shelly DUO RGBW



16 MILLION COLORS



WARM AND COLD LIGHT



Wi-Fi operated

Connect Shelly Bulb to your Wi-Fi at home.



Energy efficient

Reduce energy usage without brightness or quality loss.



16 million colors

Set the mood by choosing between 16 million colors.



Light temperature control

Easily set the desired light temperature.



Control remotely

Turn Shelly Bulb RGBW ON/OFF directly from your smartphone or tablet, and manage them easily no matter where you are.



Weekly Schedules

Easily create custom daily schedules and smart timers.



Sunrise/Sunset

Set Shelly Bulb RGBW to automatically turn ON/OFF based on sunrise and sunset hours.



No hub required

Control directly and without a hub through your smartphone with Shelly Cloud App.



Highly compatible

Use with your preferred home automation platforms and voice assistants.

SMART RGBW BULB WITH 16 MILLION COLORS

Shelly Bulb RGBW allows customers to control and adjust the brightness and the color of their light, choosing between 16 million colors. Shelly Bulb RGBW connects directly to the Wi-Fi at home and allows setting custom schedules, smart scenarios and Sunrise/Sunset actions.

TECHNICAL SPECIFICATIONS

	Shelly DUO	Shelly DUO GU10
Power supply	110-230 VAC ±10%, 50/60 Hz	
Socket	E27	GU10
Power Rating	9 W	5 W
Brightness	Warm White: 475 lm	Warm White: 475 lm
Color Temperature	3000K - 6500 K	3000K - 6500 K
Working temperature	-10°C ÷ 40°C	-10°C ÷ 40°C
Beam Angle	270°	36°
Complies with EU standards	<ul style="list-style-type: none"> • RED 2014/53/EU • LVD 2014/35/EU • EMC 2014/30/EU • RoHS2 2011/65/EU 	
Max RF power	15 dBm	
Radio protocol	Wi-Fi 802.11 b/g/n	
Frequency	2401- 2495 MHz	
Operational range (depending on local construction)	<ul style="list-style-type: none"> • up to 15 m outdoors • up to 8 m indoors 	
Dimensions	60x122 mm	50x73 mm
Electrical consumption	< 1 W	
SAR	1.10 W/Kg	

