


Optix Recessed 600x600 Medium Output


OPTIX RECESSED 600x600 2L 3000K WHT DALI

2023573



Product features

- OPTIX RECESSED 600x600 2L 3000K WHT DALI is a high efficacy low glare luminaire for office and education applications. Ceiling recessed 600x600 mm. White plastic low glare optics in 2 lines configuration. White RAL9016 fixture body. DALI dimmable. 3000K Warm White LED, CRI>80, chromaticity tolerance of 3-step MacAdam ellipse. Luminous flux 3450lm. Power consumption 26W. Luminaire efficacy 133lm/W. Lifespan: 48,500 hours L90B10. UGR<19, Luminance at 65°<3000 Cd/m2, IK07, IP20. Photobiological safety risk group 1. Electrical protection Class I. Glow wire test 850°C.




PRODUCT OVERVIEW

Product name	OPTIX RECESSED 600x600 2L 3000K WHT DALI
Technology	LED (3 SDCM)
Cap/Base	N/A
Housing	Steel
Mount	Ceiling recessed mounting
Fixture rating	Enclosed
General application	Education, Office
ETIM Class	EC002892
Warranty	5 years
Fixture luminous flux (lm)	3450
Luminous flux (lm)	3450
Luminaire efficacy (lm/W)	133
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM3
Glare control	< 19
Photobiological Risk Group	RG1
Total power consumption (W)	26
Electrical protection	Class I
Control gear type	Other
Dimmable	Yes
Dimming method	DALI
LED Flickering Rate	Ultra low (5% or less)
Housing colour	RAL 9016 - Traffic white / Bezel
IP rating	IP20
IK rating	IK07
Product EAN number	5025768235735

PHOTOMETRY

Optix Recessed 600x600 Medium Output
OPTIX RECESSED 600x600 2L 3000K WHT DALI
2023573



TECHNICAL DRAWINGS

