













Photo	Part number	Description	Target application	MI 3360	MI 3309 BT	MI 3311	A 1322	A 1422	MI 3394	MI 3321
	A 1499	External power supply 24V	If the LED tower lamp is used in combination with CE MultitesterXA the external power supply should be used.						•	
	A 1079	Discharge time cable	Adaptor for measuring discharge time on internal electronic components.						•	
	A 1060	Power splitter for discharge time measurement	T-type power splitter for measurements of discharge time on machinery and switchgear.						•	•
	S 1058	Continuity test lead, 2 x 10 m, 2 pcs	Extension test leads for continuity measurements.						•	
	S 2073	HV test lead 5m, without pistols	High voltage extension test leads for measurements on larger electrical equipment.						•	
	S 2078	HV test lead 2m, with pistols, 2pcs	High voltage test leads with pistols for measurements on larger electrical equipment.						•	•
	S 1072	Continuity test lead with crocodile clip, 2 x 2.5 m, 2 pcs	Extension test leads with protection shield and with crocodile clips for continuity testing with high test currents (10 A, 25 A).						•	
	S 2012	Continuity test lead, 10 m, 2 pcs (red, black)	2 pieces of extension test lead for continuity measurements.						•	•
	S 2025	Test lead, 1.5 m, 2 pcs (black, red)	Connection leads for different measurements.						•	•
	A 1059	Insulation and Continuity adapter	1-phase 16 A CEE plug adapter for insulation resistance and continuity measurements.						•	
	A 1447	PRCD Extension adapter	Adapter for testing of PRCD-S/K, supported from HW4.						•	
	A 1153	Test lead, black, 20 m	Extension test lead for earth and continuity measurements.		•	•	•	•	•	•

• Option