


MSVD POWER SOCKET NEMA (GFCI)

Mounting rail

USA (2 × NEMA-GFCI 5-20)
(Ground Fault Circuit Interrupter)
Screw terminals
LED (yellow)

Each socket can be loaded with 20 A, however, the total load of both sockets must be below 30 A.

[Link to Product](#)**Illustration**

Product may differ from Image

Approvals**Technical Data**

Operating voltage	max. 125 V AC
Operating current	max. 20 A
Trip level	4...6 mA

General data

Mounting method	DIN-rail mountable (EN 60715)
Connection	Screw terminals: max. 6 mm ²
Dimensions H × W × D	126×64×55 mm

Commercial data

country of origin	CZ
customs tariff number	85369010
minimum order quantity	1