

Product information

87 51 250

KNIPEX Cobra® ES

Water Pump Pliers extra-slim

DIN ISO 8976



- Ideal for service, maintenance and equipment repair, in automotive and general industry
- Long, narrow jaws
- Particularly good access to the workpiece due to very slim construction of head and joint area
- Firm grip also on flat material due to three-point rest
- Push the button for adjustment on the workpiece
- Fine adjustment for optimum adaptation to different sizes of workpieces and a comfortable handle width
- Self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- Box-joint design for high stability due to double guide
- Reliable catching of the hinge bolt: no unintentional shifting
- Favourable lever action: optimum transmission of force
- Pinch guard prevents operators' fingers being pinched
- Chrome vanadium electric steel, forged, multi stage oil-hardened

General

Article No.	87 51 250
EAN	4003773061267
Pliers	grey atramentized
Head	polished
Handles	with non-slip plastic coating
Weight	328 g
Dimensions	250 x 43 x 16 mm
Standard	DIN ISO 8976
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Adjustment positions	19
Capacities for nuts	Ø 1 1/4
Capacities for nuts	34 mm
Capacities for pipes (diameter)	Ø 32 mm
max. parallel opening width	37 mm
max. gripping depth	42 mm

technical change and errors excepted



Optimum access to the workpiece. Ideal for service, maintenance and equipment repair, in automotive and general industry. Very slim design in the complete head and joint area (compared to conventional water pump pliers)

