


Stauffer Grease Boxes DIN 3411 version A

Material: Steel, blued. Top and bottom part drawn, with rolled spigot screw thread.



Ordering Details: e.g.: Product No. 68000100, Stauffer Grease Box DIN 3411, Gr. 1


Product No.	Size	Thread Inch	Volume cm ³	SW mm	D mm	b _{max.} mm	h _{max.} mm	Weight mm
680 001 00	1	R 1/8"	2,2	12	18	9	35	15
680 002 00	2	R 1/4"	5	17	26	11	38	30
680 003 00	3	R 1/4"	10	17	32	11	42	45
680 004 00	4	R 1/4"	17	17	38	11	45	55
680 005 00	5	R 1/4"	35	17	49	11	52	85
680 006 00	6	R 1/4"	50	17	58	11	56	115

Extensions G1/4" R1/4"

Material: Brass.
Steel, zinc-plated.

Extension with Whitworth pipe thread 1/4", suitable for e.g.:

- Flange bearings DIN 502 A, DIN 502 B and DIN 503.
- Pillow block bearings DIN 504 A, DIN 504 B and DIN 505.
- Lubricators.
- Drip-feed oilers Unikum and UNI, sizes with R1/4".
- Stauffer grease boxes, sizes with R1/4".



Ordering Details: e.g.: Product No. 68054300, Extension 30mm


Product No.	Extension mm	L mm	Internal Thread	External Thread	Material	Weight g
680 543 00	30	40	G 1/4"	G 1/4"	Brass	25
680 543 50	40	50	G 1/4"	R 1/4"	Steel zinc-plated	42
680 543 65	55	65	G 1/4"	R 1/4"	Steel zinc-plated	54

Oil-Level Windows SR

Material: Aluminium with inserted disk of natural glass and NBR seal.

Rectangular shape, clear readability.
Also diesel-oil resistant.

Temperature resistant up to +120°C.



Ordering Details: e.g.: Product No. 68113000, Oil-Level Window SR 60, 39 x 18 mm

Product No.	Type	Sight mm	L x Width mm	Mounting Holes Quantity x mm	X mm	Weight g
681 130 00	SR 60	39 x 18	60 x 45	4 x Ø 5,5	28	55
681 131 00	SR 80	59 x 18	80 x 45	4 x Ø 5,5	45	84
681 132 00	SR 100	79 x 18	100 x 45	6 x Ø 5,5	35	108
681 133 00	SR 125	104 x 18	125 x 45	6 x Ø 5,5	45	135
681 134 00	SR 160	139 x 18	160 x 45	8 x Ø 5,5	40	170
681 135 00	SR 200	179 x 18	200 x 45	10 x Ø 5,5	40	210
681 136 00	SR 250	229 x 18	250 x 45	12 x Ø 5,5	40	270