

Pneumatic belt sander GB 14000

**MANNESMANN
DEMAG**

Application:

For sanding on free belt or with belt support contact

Execution:

- With sanding belt cooling
- With replaceable contact arms
- For 6-mm and 13-mm belt widths
- Exhaust: front

Delivery:

Sanding arm 610x13mm, hose unit



Art. no.	75061 160
Brand	MANNESMANN DEMAG
Manufacturer Part Number	60011256
Model	GB 1400
Valve design	Lever valve
Max. belt speed	20 m/s
Max. idle speed	20000 rpm
Power input	400 W
Air consumption	14.1 l/s
Connection thread	IT 1/4 inch
Length	371 mm
Min. sanding belt width	6 mm
Max. sanding belt width	13 mm
Weight	1.4 kg
Grinding belt length	610
Gross Weight	1.400 kg
Product Group	7AA

EAN

4251757302800