

Pneumatic impact screwdriver 9012LGTT

Square drive 1/2-in – long spindle



Execution:

- Spindle length 186 mm for reaching deep screw connections
- Removable support bracket 360°, adjustable
- 3 power levels in clockwise rotation, 1 power level in anti-clockwise rotation
- Cold-insulating handle

Advantage:

- low-vibration
- One-handed operation for left-handed and right-handed users

Delivery:

Includes Coupling connector



Art. no.	75065 043
Brand	HAZET
Manufacturer Part Number	9013LGTT
Model	9013 LGTT
Suitable for screw	M32
Max. tightening torque	2020 Nm
Max. releasing torque	3800 Nm
Max. idle speed	5200 rpm
Air consumption	243 l/min
Tool holding device	3/4-inch external square
Hammer mechanism system	High-performance twin hammer mechanism
Length	370 mm
Connection thread	IT 3/8 inch
Inner hose diameter	13 mm
Operating pressure	6.3 bar
Sound-pressure level	102.5
Weight	5.5 kg
With right/left-hand rotation	Yes
Gross Weight	5.700 kg
Product Group	738

EAN

4000896232277