

Spherical washers, DIN 6319 C

Steel, tempered to 350 + 80RV30



Application:

For transferring clamping forces in cases where clamping elements need to adapt to uneven clamping surfaces.

Execution:

- Case-hardened and phosphatised



Art. no.	26208 514
Brand	AMF
Manufacturer Part Number	81745
Suitable cheese-head screw DIN 912	M10
Outer diameter	21 mm
Internal diameter	10.5 mm
Max. washer height	4 mm
Radius	15 mm
DIN	6319
Gross Weight	0.006 kg
Product Group	260

EAN

4020772081744