

Product Image



/publicpictures/Produktbild/1208478501.tif

Master data

Product number:	1208478501
EAN:	4007123114726
Artikelverantwortlicher:	Brennenstuhl Tübingen
manufacturer:	Brennenstuhl
Product line:	
Kundenspezifisch:	No
Minimalpflege:	No
Ausleitungskennzeichen:	J
Gewählte Vertriebsregion:	De
Gewählte Sprache:	en

Texts

Is4-Bezeichnung 12:

K-Tro. Garant 290 40m N05V3V3-F3G1,5 blau, 4fach/Thermo <IP44> *DK*

Short description for the internet:

Website-Kurztext:

Print-Kurztext:

Garant IP44 cable reel 40m AT-N05V3V3-F3G1,5 *DK*

Bulletpoint 1:

Bulletpoint 2:

Bulletpoint 3:

Bulletpoint 4:

Bulletpoint 5:

Online-Beschreibung:

Website description:

Schlagworte:

Subtitle:

Practical and suitable for outdoor use, IP 44.

Print-Beschreibung:

* For use all around the house.

* The BREMAXX®-cable is extremely sturdy, applicable down to -35°C, oil- and UV-resistant and highly abrasion-resistant.

* Reel body made from special plastic fitted to a galvanised steel tube frame.

* 4 water-jet protected earthed socket outlets with self-closing protective caps.

* Ergonomic cable guide handle for perfect cable-management during winding.

* Danish Standard.

Infotext:

Design protected.

Table article information:

Scope of supply:

Media



/publicpictures/Logo-Brennenstuhl/logo-made-in-germany.eps



/publicpictures/icon/icon-schutzart-ip44.eps



/publicpictures/icon/icon-stecksystem-dk-erdung.eps

Context

Attributkategorie:	Cable Reel	Accessories:	1081000
Garantie:	Other (legal)	Ersatzteil:	

Technical data

Kabel		Kabeltrommel	
Cable designation:	AT-N05V3V3-F 3G1,5	Capacity in uncoiled state 230V:	3,000W
Cable length:	40m	Nominal input voltage:	230 V
Additional cable length:	0m	Max. current carrying capacity:	13A
Cable colour:	red	With residual current circuit breaker (RCCB):	No
Cable entry into the housing:	Cable bend relief	With test button:	No
Low temperature resistant:	Yes	With miniature fuse:	No
Kabeltrommel		Protection:	Not applicable
Usage:	outdoor	Number of socket outlets total:	4
Housing material:	Plastic	Increased touch protection:	Yes
Housing colour:	blue	With hinged lid/ cover:	Yes
Colour:	blue		

		Plug system socket:	Type K (DK)
Reel diameter:	290mm	Plug system CEE socket:	Without
With on/off switch:	No	With plug:	Yes
With frame:	Yes	With plug storage:	Yes
With adjustment - e:	Yes	Plug system plug:	Type K (DK)
With carrying handle:	Yes	Coupling/ power block:	Without
Material of the carrying handle :	Plastic	Hammer sign:	No
With turn handle:	Yes	Regulation/ standard:	
With standby display :	No	Mgv	
With control lamp:	No	Packaging unit (UP):	1
With overheating protection:	Yes	Weight of product (without packaging):	6.24kg
With radio:	No	Length of product (without packaging):	19cm
With loudspeaker:	No	Width of product (without packaging):	29cm
With ROL 'UP':	No	Height of product (without packaging):	36cm
Automatic cable winding:	No	Weight of product (including packaging):	6.25kg
With Bretec:	No	Length of product (including packaging):	19cm
With CABLEPILOT:	Yes	Width of product (including packaging):	29cm
Mit Isolierscheiben:	No	Height of product (including packaging):	36cm
With vehicle:	No		
Cable station:	No		
Suitable for wall mounting:	No		
Packaging:			
Degree of protection (IP):	IP44		
Area of use:	outdoor		
Protection class:	II		
Nominal frequency:	~		
Capacity in coiled state 230V:	900W		

Variantgroup

Garant® IP 44 Cable Reel

* For use all around the house.

- * The BREMAXX®-cable is extremely sturdy, applicable down to -35°C, oil- and UV-resistant and highly abrasion-resistant.
- * Reel body made from special plastic fitted to a galvanised steel tube frame.
- * 4 water-jet protected earthed socket outlets with self-closing protective caps.
- * Ergonomic cable guide handle for perfect cable-management during winding.
- * Danish Standard.

Related Article

1218378501

1208478501

Variant Differentiation

Objektbrick Kabel: Attribut cable_length

Objektbrick Kabeltrommel: Attribut drum_diameter