



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

| LOC | | DIST | | REVISIONS | | | |
|-----|-----|-----------------------|---------|-----------|------|--|--|
| P | LTR | DESCRIPTION | DATE | DWN | APVD | | |
| CM | 00 | | | | | | |
| | Y | REV PER ECO-07-003708 | 21FEB07 | KW | DB | | |

| | | | |
|-----|--------------|----|------------|
| YES | 71.12[2.800] | 28 | 5-640442-8 |
| YES | 68.58[2.700] | 27 | 5-640442-7 |
| YES | 66.04[2.600] | 26 | 5-640442-6 |
| YES | 63.50[2.500] | 25 | 5-640442-5 |
| YES | 60.96[2.400] | 24 | 5-640442-4 |
| YES | 58.42[2.300] | 23 | 5-640442-3 |
| YES | 55.88[2.200] | 22 | 5-640442-2 |
| YES | 53.34[2.100] | 21 | 5-640442-1 |
| YES | 50.80[2.000] | 20 | 5-640442-0 |
| YES | 48.26[1.900] | 19 | 4-640442-9 |
| YES | 45.72[1.800] | 18 | 4-640442-8 |
| YES | 43.18[1.700] | 17 | 4-640442-7 |
| YES | 40.64[1.600] | 16 | 4-640442-6 |
| YES | 38.10[1.500] | 15 | 4-640442-5 |
| YES | 35.56[1.400] | 14 | 4-640442-4 |
| YES | 33.02[1.300] | 13 | 4-640442-3 |
| YES | 30.48[1.200] | 12 | 4-640442-2 |
| YES | 27.94[1.100] | 11 | 4-640442-1 |
| YES | 25.40[1.000] | 10 | 4-640442-0 |
| YES | 22.86[.900] | 9 | 3-640442-9 |
| YES | 20.32[.800] | 8 | 3-640442-8 |
| YES | 17.78[.700] | 7 | 3-640442-7 |
| YES | 15.24[.600] | 6 | 3-640442-6 |
| YES | 12.70[.500] | 5 | 3-640442-5 |
| YES | 10.16[.400] | 4 | 3-640442-4 |
| YES | 7.62[.300] | 3 | 3-640442-3 |
| YES | 5.08[.200] | 2 | 3-640442-2 |

| | | | |
|----|--------------|----|------------|
| NO | 71.12[2.800] | 28 | 2-640442-8 |
| NO | 68.58[2.700] | 27 | 2-640442-7 |
| NO | 66.04[2.600] | 26 | 2-640442-6 |
| NO | 63.50[2.500] | 25 | 2-640442-5 |
| NO | 60.96[2.400] | 24 | 2-640442-4 |
| NO | 58.42[2.300] | 23 | 2-640442-3 |
| NO | 55.88[2.200] | 22 | 2-640442-2 |
| NO | 53.34[2.100] | 21 | 2-640442-1 |
| NO | 50.80[2.000] | 20 | 2-640442-0 |
| NO | 48.26[1.900] | 19 | 1-640442-9 |
| NO | 45.72[1.800] | 18 | 1-640442-8 |
| NO | 43.18[1.700] | 17 | 1-640442-7 |
| NO | 40.64[1.600] | 16 | 1-640442-6 |
| NO | 38.10[1.500] | 15 | 1-640442-5 |
| NO | 35.56[1.400] | 14 | 1-640442-4 |
| NO | 33.02[1.300] | 13 | 1-640442-3 |
| NO | 30.48[1.200] | 12 | 1-640442-2 |
| NO | 27.94[1.100] | 11 | 1-640442-1 |
| NO | 25.40[1.000] | 10 | 1-640442-0 |
| NO | 22.86[.900] | 9 | 640442-9 |
| NO | 20.32[.800] | 8 | 640442-8 |
| NO | 17.78[.700] | 7 | 640442-7 |
| NO | 15.24[.600] | 6 | 640442-6 |
| NO | 12.70[.500] | 5 | 640442-5 |
| NO | 10.16[.400] | 4 | 640442-4 |
| NO | 7.62[.300] | 3 | 640442-3 |
| NO | 5.08[.200] | 2 | 640442-2 |

LEADFREE DIM A NO. OF CIRCUITS PART NO.



1 MATERIAL: CONNECTOR - NYLON UL94V-2 (BLUE).
 CONTACTS - 0.30[.012] THICK COPPER ALLOY
 BRIGHT TIN-LEAD .00203[.000080] MIN THICKNESS
 FOR 640442-2 THRU 2-640442-8.
 MATTE WHISKER MITIGATED TIN .00203[.000080] MIN THICKNESS
 OVER NICKEL UNDERPLATE FOR 3-640442-2 THRU 5-640442-8.

- 2. CONTACTS ACCEPT 26 AWG WIRE WITH 1.52[.060] MAX INSULATION DIAMETER.
- 3. CONTACTS MUST ACCEPT 0.64±0.03[.025] POST AND REMAIN LOCKED IN POSITION.
- 4 IDENTIFICATION NUMBER FOR LAST CIRCUIT MAY NOT APPEAR ON ALL ASSEMBLIES.
- 5. DIMENSIONS IN BRACKETS ARE IN INCHES.
- 6. HOUSING FEATURES ARE: CLOSED END WITH LOCKING RAMP.

METRIC

| | | | | |
|---|--|----------------------------------|---|--------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. | | DWN S. CARPENTER 10JUN2003 | Tyco Electronics Corporation Harrisburg, PA 17105-3608 | |
| DIMENSIONS: mm [INCHES] | | CHK D. BOSSI 10JUN2003 | NAME MTA 100 CONNECTOR ASSEMBLY, 26 AWG, STANDARD | |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 0.13 [.005] 4 PLC ± ANGLES ± FINISH 1 | | APVD D. BOSSI 10JUN2003 | APPLICATION SPEC 108-1050 114-1019 | |
| MATERIAL 1 | | PRODUCT SPEC | SIZE A2 | CAGE CODE 00779 |
| | | WEIGHT | DRAWING NO C=640442 | RESTRICTED TO - |
| | | CUSTOMER DRAWING | SCALE 5:1 | SHEET 1 of 1 |
| | | | REV Y | |