

KERN DE 120K10A

The long lasting story of success with dust and spray protected display device



Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

Power supply

Battery:	9 V Block
Charging time:	10 h
Input voltage:	220 V - 240 V AC 50 Hz
Mains adapter:	Mains adapter external
Mains adapter/adapter included:	EURO CH UK US
Operating time:	12 h
Operating time (Backlight off):	30 h
Operating time (Backlight on):	15 h
Rechargeable battery:	Rchrg. battery optional

Services (optional)

Adjustment at the location of installation: 961-249

DAkkS Certificate:	963-129
--------------------	---------

Category

Brand:	KERN
Category:	Balances

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	515 x 395 x 140 mm
Gross weight:	5,700 kg
Net weight:	4,900 kg
Shipping method:	Parcel service

Construction

Cable length of display device:	1,400 m
Dimensions housing (WxDxH):	315 x 305 x 75 mm
Dimensions of display device (WxDxH):	225 x 110 x 45 mm
Dimensions of weighing plate (WxDxH):	318 x 308 x 75 mm
Material weighing plate:	stainless steel
Weighing surface (WxD):	315 x 305 mm

Measuring system

Adjustment options:	External calibration
Linearity:	30 g
Readability [d]:	10 g
Recommended adjusting weight:	120 kg (M1)
Repeatability:	10 g
Resolution:	12000
Stabilisation time under laboratory conditions:	2,500 s
Tare range:	120 kg
Warm up time:	30 min
Weighing capacity [Max]:	120 kg
Weighing system:	Strain gauge
Weighing units:	tl (HK) tol mo lb dwt ffa oz tl (Tw) kg ozt

Display

Display digit height (large):	2,500 cm
-------------------------------	----------

Counting

Counting resolution:	6000
Minimum piece weight at piece counting (Laboratory):	20 g
Minimum piece weight at piece counting (Normal):	200 g

Functions

Counting function:	yes
Percentage determination:	yes
Vibration-free weighing (Animal weighing program):	yes


KERN DE 120K10A



The long lasting story of success with dust and spray protected display device

Piktogramme

STANDARD



OPTION

