

Boring bar AMI right

For internal recessing and copy turning using AD and AE cutting inserts

ATORN

Application:

For recessing and copy turning, internal

Execution:

- Precision-manufactured steel support, nickel-plated and hardened with clamping element



Art. no.	17673 776
Brand	ATORN
Manufacturer Part Number	12371014
Suitable for knife width	4 mm
Shank diameter	40 mm
Plunge depth	12 mm
Length	300 mm
Immersion depth	12 mm
Clamping surface height	38.5 mm
Adjustment rate via centre	32.5 mm
Min. bore diameter	51.7 mm
Tool design	Right
Gross Weight	1.516 kg
Product Group	1FF

EAN

4050293740387

