

WE-LHMI

SMD Low Profile High Current Molded Inductor



1040	744 373 680 022 L: 0.22 μ H I_R : 24.0 A I_{sat} : 70.0 A $R_{DC typ}$: 0.8 m Ω	744 373 680 036 L: 0.36 μ H I_R : 21.0 A I_{sat} : 64.0 A $R_{DC typ}$: 1.05 m Ω	744 373 680 039 L: 0.39 μ H I_R : 20.5 A I_{sat} : 63.0 A $R_{DC typ}$: 1.1 m Ω	744 373 680 045 L: 0.45 μ H I_R : 20.0 A I_{sat} : 50.0 A $R_{DC typ}$: 1.3 m Ω	744 373 680 056 L: 0.56 μ H I_R : 19.0 A I_{sat} : 44.0 A $R_{DC typ}$: 1.6 m Ω	744 373 680 068 L: 0.68 μ H I_R : 16.0 A I_{sat} : 42.0 A $R_{DC typ}$: 2.4 m Ω	744 373 680 10 L: 1.0 μ H I_R : 14.5 A I_{sat} : 36.0 A $R_{DC typ}$: 3.0 m Ω
	744 373 680 22 L: 2.2 μ H I_R : 10.0 A I_{sat} : 28.0 A $R_{DC typ}$: 6.5 m Ω	744 373 680 33 L: 3.3 μ H I_R : 8.0 A I_{sat} : 23.0 A $R_{DC typ}$: 10.8 m Ω	744 373 680 39 L: 3.9 μ H I_R : 7.5 A I_{sat} : 19.5 A $R_{DC typ}$: 12.6 m Ω	744 373 680 47 L: 4.7 μ H I_R : 7.0 A I_{sat} : 19.0 A $R_{DC typ}$: 15.0 m Ω	744 373 680 68 L: 6.8 μ H I_R : 6.0 A I_{sat} : 14.0 A $R_{DC typ}$: 17.5 m Ω	744 373 681 00 L: 10.0 μ H I_R : 5.2 A I_{sat} : 12.5 A $R_{DC typ}$: 27.0 m Ω	744 373 681 50 L: 15.0 μ H I_R : 4.1 A I_{sat} : 8.5 A $R_{DC typ}$: 40.0 m Ω
	744 373 682 20 L: 22.0 μ H I_R : 3.5 A I_{sat} : 8.0 A $R_{DC typ}$: 64.0 m Ω	744 373 683 30 L: 33.0 μ H I_R : 2.6 A I_{sat} : 5.0 A $R_{DC typ}$: 92.0 m Ω	744 373 684 70 L: 47.0 μ H I_R : 2.2 A I_{sat} : 4.5 A $R_{DC typ}$: 145.0 m Ω				
	744 373 770 022 L: 0.22 μ H I_R : 25.0 A I_{sat} : 40.0 A $R_{DC typ}$: 0.75 m Ω	744 373 770 033 L: 0.33 μ H I_R : 24.0 A I_{sat} : 35.0 A $R_{DC typ}$: 0.88 m Ω	744 373 770 047 L: 0.47 μ H I_R : 19.0 A I_{sat} : 29.0 A $R_{DC typ}$: 1.32 m Ω	744 373 770 056 L: 0.56 μ H I_R : 18.5 A I_{sat} : 28.0 A $R_{DC typ}$: 1.40 m Ω	744 373 770 068 L: 0.68 μ H I_R : 17.5 A I_{sat} : 27.0 A $R_{DC typ}$: 1.80 m Ω	744 373 770 10 L: 1.0 μ H I_R : 15.0 A I_{sat} : 26.0 A $R_{DC typ}$: 2.70 m Ω	744 373 770 15 L: 1.50 μ H I_R : 12.5 A I_{sat} : 25.5 A $R_{DC typ}$: 4.70 m Ω
	744 373 770 22 L: 2.20 μ H I_R : 10.0 A I_{sat} : 25.0 A $R_{DC typ}$: 7.20 m Ω	744 373 770 33 L: 3.30 μ H I_R : 9.5 A I_{sat} : 24.5 A $R_{DC typ}$: 9.0 m Ω	744 373 770 47 L: 4.70 μ H I_R : 7.5 A I_{sat} : 18.0 A $R_{DC typ}$: 13.0 m Ω				
1335							

EMC COMPONENTS | **INDUCTORS** | TRANSFORMERS | RF COMPONENTS | CIRCUIT PROTECTION | EMC SHIELDING MATERIAL | CONNECTORS | SWITCHES | ASSEMBLY TECHNIQUE | POWER ELEMENTS

Important information: Würth Elektronik's design kits contain reference components. These components correspond with the current product development status on the day of supply. Exchange of the reference components to components with up-to-date product development status is not carried out automatically. No liability is taken for the use of these reference components. Therefore, please request new samples prior to releases for series production and product release.

Please check datasheets on www.we-online.com for specifications. Würth Elektronik eiSos GmbH & Co. KG, EMC & Inductive Solutions. © 2014

All products
in stock!