

CONNECTING CABLE FOR MOBILE PANELS (MPI/PROFIBUS),  
SPECIAL LENGTH 15 M



Figure similar

<b>Product type designation</b>	
<b>Supply voltage</b>	
Rated value (DC)	24 V; DC
<b>Degree and class of protection</b>	
IP (at the front)	IP65
IP (rear)	IP65
<b>Standards, approvals, certificates</b>	
CE mark	Yes
Suitable for safety functions	Yes; e.g. emergency stop, acknowledgment button
<b>Ambient conditions</b>	
<b>Ambient temperature in operation</b>	
• Min.	0 °C
• max.	55 °C
<b>Storage/transport temperature</b>	
• Min.	-40 °C
• max.	70 °C
<b>Relative humidity</b>	
• Operation, max.	85 %
<b>Cables</b>	
Smallest bending radius	45 mm
Oil resistance of outer sheath	Yes; Hydrolysis-resistant and oil-resistant acc. to VDE 0472 Part 803/B, also resistant to commercially available lubricants and hydraulic oils

Resistance to MEK, xylene, toluene, isopropanol	Yes
Color of cable sheath	Red
<b>Mechanics/material</b>	
Material of cable sheath	Special PUR, flame-resistant acc. to VDE 0472 Part 804 Test Type B, Shore A 88 Flame-Retardant UR Style 20963
<b>Dimensions</b>	
Thickness	9 mm
<b>Scope of supply</b>	
Delivery unit in items	1
<b>other</b>	
Note:	Length 15 m
<b>last modified:</b>	12.03.2015