



## MEHRBEREICHSBLINDNIETE GROSSKOPF

## MULTIGRIP BLIND RIVETS LARGE HEAD


## RIVETS MULTI SERRAGE TÊTE LARGE









Aluminium AIMG 2,5  
Aluminium AIMG 2,5  
Aluminium AIMG 2,5


Edelstahl A2 [ 1.4301 ]  
Stainless steel A2 [ AISI 304 ]  
Acier inox A2 [ 1.4301 ]







### Ø 4,0 mm D2 = 12,0 mm

D1 = 4,0 + 0,05 / - 0,13 mm  
D2 = 12,0 +/- 0,5 mm  
k = ≤ 2,5 mm  
d = 2,18 mm  
P = ≥ 27,0 mm  
L = + 1,0 / - 0,2 mm  
 4,1 mm

	F-Max		CODE				
4,0 x 9,5 mm	13,5 mm	1,2 - 6,4 mm	77703 40950	1050 N	1300 N	500	5000
4,0 x 12,7 mm	16,7 mm	4,0 - 9,5 mm	77703 40125			500	5000
4,0 x 16,9 mm	21,0 mm	8,5 - 13,5 mm	77703 40170			500	5000

### Ø 4,8 mm D2 = 16,0 mm

D1 = 4,8 + 0,05 / - 0,13 mm  
D2 = 16,0 +/- 0,5 mm  
k = ≤ 2,5 mm  
d = 2,78 mm  
P = ≥ 27,0 mm  
L = + 1,0 / - 0,2 mm  
 4,9 mm

	F-Max		CODE				
4,8 x 10,3 mm	14,8 mm	1,6 - 6,4 mm	77703 48103	1400 N	2000 N	250	2500
4,8 x 15,1 mm	19,6 mm	4,8 - 11,0 mm	77703 48151			250	2500
4,8 x 16,9 mm	21,4 mm	6,4 - 12,7 mm	77701 48169			250	2500
4,8 x 24,8 mm	29,3 mm	12,7 - 19,8 mm	77703 48248			250	2500