

Clamping screw sets



Execution:

- Tempered
- Strength class 8 or 10
- Different clamping heights can be set as required using extension nuts and studs (extension studs).
- Widths across flats are in accordance with ISO standard (DIN ISO 272)

Delivery:

In a sturdy, high-quality wooden box with removable hinged lid.



Art. no.	26209 120
Brand	AMF
Manufacturer Part Number	82990
Suitable for groove width	12 mm
Thread dimension	M12
Number of DIN 787 T-slot screws	2 x M12 x 50 mm, 4 x M12 x 80 mm, 4 x M12 x 125 mm
Number of DIN 6379 stud bolts (extension pin)	4 x M12 x 63 mm, 4 x M12 x 100 mm, 4 x M12 x 200 mm
Number of DIN 6330 B high nuts	4 PCS
Number of extension nuts	4 PCS
Wooden box length	278 mm
Wooden box width	234 mm
Wooden box height	36 mm
Gross Weight	3.400 kg
Product Group	260

EAN

4020772082994