

ToLEDo Stick

TOLEDO STICK 500LM 840 E27 SL

0029927



Product features

- A bright, all-around lighting solution for living rooms, wall lights, ceiling lights, compact and decorative luminaires • Quick and easy replacement of 40W incandescent lamp • 15,000H average rated life - last 15X longer than incandescent/halogen lamps • 87% energy savings compared to incandescent • Last 50% longer and consume 45% less energy compared to compact fluorescent integrated lamps • A++ energy rating • 100 lm/W • Omni-directional light distribution • Non-dimmable



PRODUCT OVERVIEW

Product name	TOLEDO STICK 500LM 840 E27 SL
Technology	LED
Watt (Rated) (W)	6
Type	ToLEDo GLS
Cap/Base	E27
Fixture rating	Open
General application	Hospitality, Residential & Consumer
ETIM Class	EC001959
E-number FI	4740648
Warranty	3 years
Luminous flux (lm)	500
Colour temperature (K)	4000
Light colour	Cool White
CRI (Ra)	80
Beam Angle (°)	240
Wattage (W)	6
Product Voltage (V)	230
Average life (Nominal) (h)	15000
Product EAN number	5410288299273

DATA TABLE

General data

Product name	TOLEDO STICK 500LM 840 E27 SL
Technology	LED
Watt (Rated) (W)	6
Type	ToLEDo GLS
Cap/Base	E27
Fixture rating	Open
General application	Hospitality, Residential & Consumer
Performance ambient temperature Tq (°C)	25
ETIM Class	EC001959
E-number FI	4740648
Warranty	3 years

ToLEDo Stick

TOLEDO STICK 500LM 840 E27 SL

0029927

Optical data

Luminous flux (lm)	500
Luminous flux (Rated) (lm)	500
Colour temperature (K)	4000
Light colour	Cool White
CRI (Ra)	80
Beam Angle (°)	240
Lumen maintenance at end of nominal life (%)	70

Electrical data

Wattage (W)	6
Starting time (max) (s)	0.5
Warm-up time to 60% of full light (max) (s)	0.5
Product Voltage (V)	230
Lamp power factor	0.5
No. Of switching cycles before premature failures	>50000
Inrush Current (A)	2.01
kWh per 1000 hours burning time	6
Nominal Frequency (Hz)	50/60Hz
Max. Luminaires per 10A C Breaker	25
Max. Luminaires per 16A C Breaker	40
Max. Luminaires per 20A C Breaker	50

Lifetime data

Average life (Nominal) (h)	15000
Average life (Rated) (h)	15000

Physical data

Nominal Product Length (mm)	112
Nominal Product Diameter (mm)	37
Weight (kg)	0.042

Packaging

Single packaging type	Carton
Product EAN number	5410288299273
Packaging single length / height (cm)	11.7
Packaging single width (cm)	4.0
Packaging single depth (cm)	4.0
DUN14 (inner)	25410288299277
Units per inner package	10
Packaging inner length / height (cm)	21.5
Packaging inner width (cm)	9.0
Packaging inner depth (cm)	13.5
DUN14 (outer)	15410288299270
Units per outer package	60
Packaging outer length / height (cm)	29.2

ToLEDo Stick

TOLEDO STICK 500LM 840 E27 SL

0029927

Packaging outer width (cm)	23.0
Packaging outer depth (cm)	30.0

Safety data

Breakage cleaning instructions	Not applicable
Special purpose lamp	No
Dry applications use only	Yes
Suitable for household illumination	Yes
Safety message	Not Suitable for totally enclosed fixtures