

Elastic mounting plates

EFFBE

Application:

For non-slip anchor-free erection of machines and apparatus for which there are no means of fixing for levelling elements (no. 26400). An angled stay can be cut off for arranging in rows.

Execution:

- Elastomer body 802 C (CR 80 Shore A)
- Resistant to oil and ageing
- Non-slip

Advantage:

- No anchor points required



Art. no.	26402 020
Brand	EFFBE
Manufacturer Part Number	FB62004218
Model	EPA 10
Supporting plate length	90 mm
Supporting plate width	90 mm
Supporting plate height	13 mm
Load-carrying capacity	1500 kg
Gross Weight	0.211 kg
Product Group	265