

## USB handheld microscopes

DinoCapture measuring software

Dino-Lite  
Digital Microscope

### Application:

For industrial inspections, quality control, training, mounting, repairs and material defect analyses

### Execution:

- CMOS Color high-resolution sensor
- Adjustable LED lighting
- MicroTouch button for saving live images/videos on PC
- Record images and videos
- USB 2.0 interface
- Housing dimensions, diameter 32 x 105 mm
- DinoCapture software: 2D image measurement (line, radius, diameter, arc, polygon, angle), insertion of texts, direct output of measured data to Excel

### Advantage:

- Rapid archiving and recording of components under the USB handheld microscope
- Low-cost entry-level equipment for image viewing and measuring
- High flexibility with exchangeable attachments
- Automatic magnification reading

### Delivery:

USB handheld microscope with USB cable (L = 1.8 m), CD with DinoCapture software



<b>Art. no.</b>	<b>41613 077</b>
<b>Brand</b>	DINO-LITE
<b>Manufacturer Part Number</b>	AM7915MZT
<b>Model</b>	AM7915MZT
<b>Camera resolution</b>	5 Mpix
<b>Magnification</b>	10 to 220-times
<b>Image resolution</b>	2592 x 1944 pix
<b>Min. working distance</b>	4 mm
<b>Max. working distance</b>	136 mm
<b>Cable length</b>	1.8 m
<b>Data transmission type</b>	USB
<b>Polariser</b>	Yes
<b>Software</b>	DinoCapture
<b>Material of housing</b>	Aluminium
<b>Gross Weight</b>	0.841 kg
<b>Product Group</b>	4AC