

## TE Type K - Telescopic surface sensor

extendible up to 985 mm



### Application:

The surface temperature sensor with extendible telescope is suitable for measurements in hard-to-reach areas.

### Execution:

- Sensor type: TE Type K
- Measuring range: -50 to +250 °C
- Accuracy: Class 2 in accordance with EN 60584-2
- Response time: 3 s
- Length of probe/sensor tube: 985mm
- Length/diameter of probe/sensor tube tip: 12 mm/25 mm



<b>Art. no.</b>	<b>46108 090</b>
<b>Brand</b>	TESTO
<b>Manufacturer Part Number</b>	0602 2394
<b>Sensor type</b>	TE type K
<b>Probe type</b>	Surface probe
<b>Probe designation</b>	Telescopic surface probe
<b>Min./max. temperature measuring range</b>	-50 to 250 °C
<b>Accuracy temperature</b>	Class 2 according to EN 60584-2
<b>Response time sensor</b>	3 s
<b>Diameter sensor tube tip</b>	25 mm
<b>Length sensor tube</b>	985 mm
<b>Length sensor tube tip</b>	12 mm
<b>Cable length</b>	1.6 m
<b>EN standard</b>	60584-1
<b>Gross Weight</b>	0.260 kg
<b>Product Group</b>	4CF

### EAN

4029547002885