



Datenblatt - Fiche technique - Data sheet

11.04.5660




ROLINE Monitor-Kabel mit Ferritkern+DDC, HD15 ST-ST, 10m

ROLINE Câble écran HD15 M/M avec noyaux de ferrite + DDC, 10 m

ROLINE High Quality VGA Cable + Ferrite + DDC, HD15, M/M, 10 m


ROHS-COMPLIANT

LTR	REV.	DESCRIPTION	DATE



NOTE:

- CABLE: UL-2919 28AWG(7/0.127 T.C)*3COAX(75 OHMS) +24AWG(7/0.20 T.C)*9C+AL/MY+D.W+BRAID(85%) PVC JACKET, COLOR: BLACK(NK-K01) OD: \varnothing 8.5 \pm 0.15mm, (C2919355-1) (SPACE SHUTTLE)
- CONNECTOR:
P1&P2:HDB15P MALE, GOLD FLASH CONTACT, NICKEL PLATED SHELL
- SHIELD: COPPER-FOIL 360° SOLDERED TO CONNECTOR SHELL & CABLE BRAID
- HOOD: MOLDED TYPE, PVC 45P, COLOR: BLACK(NK-K01)
- ELECTRICAL TEST: <1>.100% OPEN SHORT & MIS WIRE TEST
<2>. CONTACT RESISTANCE 3 Ohms MAX
<3>. INSULATION RESISTANCE 10M Ohms MIN
- PACKING: <1>EACH PC / POLYBAG + BIG HEADER CARD + BAR CODE LABEL.
<2>EACH PC / POLYBAG + BAR CODE LABEL.



Tolerance	Inch	M/M
.X	.015	.30
.XX	.010	.10
.XXX	.005	.05

Drawn	FANNIE 09/24/10'	Customer P/N	HDB15/M-HDB15/M W/FERRITE CORES CABLE
Check			
Engr			

Rotronic co., LTD.

DWG	P/N	LFT(mm)	BAR CODE NO.	PACKING	CTN BAR CODE
120-3272-3	11.04.5670	20000±200	7611990192267	<2>	7611990992263
120-3272-2	11.04.5660	10000±100	7611990192250	<2>	7611990992256
120-3272-1	11.04.5653	3000±30	7611990192243	<1>	7611990992249

App'd	Customer	T-RAG
Scale	NONE	Units
Dwg No.	120-3272	REV: A
Sheet	1/1	