



12W

VT-828 12W LED WALL LIGHT COLORCODE:3000K,BLACK -SQUARE

Lumens <b>900</b>	Beam Angle <b>158</b>	Dimensions <b>169x100mm</b>
----------------------	--------------------------	--------------------------------

Warm White  
 SKU:8543



### Technical Information

Output Voltage: DC:36-40V	LED Chip Type: SMD
Watts: 12	IP Rating: IP65
Lumens: 900	Dimmable: No
Shape: Square	Warranty (Years): 2
Beam Angle: 158	PF: >0.5
Output Current: 280mA	CRI: >80
No. Of Led: 72	Operation Temperature: -25 to +50°C
Unit Color: Black	Input Power: AC:220-240V,50/60Hz
Body Type: PC	Sensor Compatibility: Yes
Long life: 20,000 Hours	

### Features

- ✓ Modern Wall lights available in sleek and stylish designs.
- ✓ Excellent heat dissipation
- ✓ Available in different color options - Warm White and Day White
- ✓ Easy installation and Maintenance
- ✓ Application: Perfect for halls, pathways, Bedroom, Kitchen etc



Note: Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

## Packaging

### Unit Details

Gross Weight(GW) Kgs	0.72
Unit CBM	0.00289

### Listing Details

EAN Code	3800157638920
Commodity Code	9405403990

### Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	400

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER

**70**

COUNTRIES