

## 3D articulated measuring stand, $\mu$ -line

815 MF



### Application:

Highest stability and rigidity for  $\mu$ -precision measurements

### Execution:

- Mechanical, maintenance-free central clamping
- Dovetail mount and holder  $\varnothing$  8 mm
- Strong adhesive magnet with prismatic base

### Advantage:

- Simple, quick operation
- High degree of manoeuvrability, exact positioning
- Precision adjustment with high repeat accuracy for measurements in the  $\mu$ -range

### Delivery:

Without precision pointer



<b>Art. no.</b>	<b>34060 228</b>
<b>Brand</b>	MAHR
<b>Manufacturer Part Number</b>	4420387
<b>Height</b>	399 mm
<b>Operation radius</b>	287 mm
<b>Adherence strength</b>	800 N
<b>Base size</b>	60 x 50 x 55 mm
<b>Max. shaft diameter</b>	120 mm
<b>Gross Weight</b>	1.974 kg
<b>Product Group</b>	305

### EAN

4059192061777