

## OUTSIDE MICROMETERS

### Description

Norms: DIN 863

### Applications

Outside Micrometer  
 Carbide surfaces, lapped, spindle hardened and ground  
 Locking lever for quick and precise fixing  
 For use in the workshop

### Strong points

Lightweight design  
 Metric graduation



### Characteristics

MDM	Measurement range mm	Reading mm	Spindle diameter mm	Resolution
13828806	0-25	0-25	6,5	0,01
13828807	25-50	25-50	6,5	0,01
13828808	50-75	50-75	6,5	0,01
13828809	75-100	75-100	6,5	0,01
13828810	100-125	100-125	6,5	0,01
13828811	125-150	125-150	6,5	0,01
13828812	150-175	150-175	6,5	0,01
13828813	175-200	175-200	6,5	0,01
13828814	200-225	200-225	6,5	0,01
13828815	225-250	225-250	6,5	0,01
13828816	250-275	250-275	6,5	0,01
13828817	275-300	275-300	6,5	0,01