

Hot air tool

# HL 1620 S

EAN 4007841 351106  
Article number 351106

 steinel



CE



VDE

## Function description

The all-rounder. The two-speed HL 1620 S hot air tool soon becomes indispensable. Ideal for drying plasterwork, shrinking on cable sleeves, thawing frozen water pipes, stripping paint, waxing skis and snowboards and much more besides. With two temperature settings: 300° and 500° C.

## Technical specifications

Temperature	300 – 500 °C
Airflow rate	240 – 450 l/min
Temperature setting	2-stage
Settings made via	multiple-stage switch
Airflow control	Settings
Programming function	No
Loc function	No
Residual heat indicator	No
Cool function	No
Motor, type	Brush motor
Heating element	Micanite heating element
Mains power supply	220 – 230 V / 50 – 60 Hz
Function, hanger	No
Function, life expectancy, motor	500 h

Function, life expectancy, heating element	500 h
Replaceable heating element	No
Restart protection	No
Temperature scanner	No
Fine dust filter	No
Thermal cut-out	Yes
Thermostat	No
ESD	No
Nozzle receiver, type	34
Cord length	2.2 m
Dimensions (L x W x H)	252 x 86 x 200 mm
PU1, net weight	0,717 kg
Manufacturer's Warranty	3 years
PU1, EAN	4007841351106

<https://www.steinell.de>

Subject to technical modifications

11.2022 Page 1 from 2

Hot air tool

# HL 1620 S

EAN 4007841 351106  
Article number 351106



## Accessories

EAN 4007841 034566	HL Tool Stand
EAN 4007841 006648	Crimp connectors - Ø 1.5 - 2.5 mm
EAN 4007841 072766	Shrink tubing III - Ø 4,8 – 12,0 mm
EAN 4007841 006662	Crimp connectors - Ø 0.1 - 6.0 mm
EAN 4007841 071318	Shrink tubing I - Ø 1,6 – 4,8 mm
EAN 4007841 006655	Crimp connectors - Ø 0.5 - 1.5 mm
EAN 4007841 071417	Shrink tubing II - Ø 4,8 – 9,5 mm
EAN 4007841 070212	Surface nozzle 75 mm
EAN 4007841 075811	Shrink tubing kit
EAN 4007841 010317	Paint Scraper Set
EAN 4007841 070113	Surface nozzle 50 mm
EAN 4007841 070311	Window nozzle 50 mm
EAN 4007841 070519	Reflector nozzle
EAN 4007841 070410	Window nozzle 75 mm