

USB handheld microscopes

DinoCapture measuring software

Dino-Lite
Digital Microscope

Application:

For industrial inspections, quality control, training, mounting, repairs and material defect analyses

Execution:

- CMOS Color high-resolution sensor
- Adjustable LED lighting
- MicroTouch button for saving live images/videos on PC
- Record images and videos
- USB 2.0 interface
- Housing dimensions, diameter 32 x 105 mm
- DinoCapture software: 2D image measurement (line, radius, diameter, arc, polygon, angle), insertion of texts, direct output of measured data to Excel

Advantage:

- Rapid archiving and recording of components under the USB handheld microscope
- Low-cost entry-level equipment for image viewing and measuring
- High flexibility with exchangeable attachments
- Automatic magnification reading

Delivery:

USB handheld microscope with USB cable (L = 1.8 m), CD with DinoCapture software



Art. no.	41613 076
Brand	DINO-LITE
Manufacturer Part Number	AM4515ZT
Model	AM4515ZT
Camera resolution	1.3 Mpix
Magnification	20 to 220-times
Image resolution	1280 x 1024 pix
Min. working distance	0.5 mm
Max. working distance	60 mm
Cable length	1.8 m
Data transmission type	USB
Polariser	Yes
Software	DinoCapture
Material of housing	Plastic
Gross Weight	0.434 kg
Product Group	4AC