

Pneumatic spiral hose

Made of PU (polyurethane)



Application:

For connection to compressed-air tools and compressed-air machines.



Execution:

- With one fixed and one rotating screwed joint with ball bearing, can also be rotated with slight pressure
- connections pre-coated with PTFE, therefore scratch-resistant
- Max. pressure: 8 bar
- Max. temperature: 70°C

Advantage:

- Extremely flexible for better handling

Art. no.	75054 015
Brand	PREVOST
Manufacturer Part Number	PUS 52
Hose length	2 m
Outer diameter of hose	8 mm
Inner hose diameter	5 mm
Connection thread	G 1/4 inch
Max. operating pressure	10 bar
Gross Weight	0.183 kg
Product Group	758

EAN

3660058026857