



THOR

SOFT FACED HAMMERS

RUBBER MALLETS



Featuring self-locking handles there are three types of rubber mallet available all in a range of sizes. Rubber mallets give a gentle but firm blow with little rebound. To DIN spec and ideal for industrial and leisure use.

STANDARD BLACK – the all purpose mallet used widely for automotive, industrial, brewery, DIY camping etc.

SOFT BLACK - for use where softer blows are required.

WHITE – Will not leave marks on work surfaces. Ideal for woodworking, builders, window frame manufacturers, shop fitting, car trim, DIY etc.

Head Size		Standard Black 90° Shore A			Soft Black 75° Shore A		White 90° Shore A		
Dia	Length	Wood Handle	Fiberglass Handle	Approx Weight	Wood Handle	Approx Weight	Wood Handle	Fiberglass Handle	Approx Weight
mm	mm	Ref No.	Ref No.	g	Ref No.	g	Ref No.	Ref No.	g
40	80	61-951	-	140	-	-	-	-	-
54	90	61-952	61-952FG	310	61-75952	300	61-952W	61-952WFG	375
64	113	61-953	61-953FG	550	61-75953	525	61-953W	61-953WFG	675
74	127	61-954	61-954FG	800	61-75954	775	61-954W	61-954WFG	970
90	139	61-957	61-957FG	1200	-	-	61-957W	61-957WFG	1450

HIDE MALLETS

Manufactured from genuine Water-Buffalo hide tightly coiled, pressed three times under powerful hydraulic presses and seasoned for many months. These carefully controlled processes ensure dependable hide mallets of uniform quality and maximum durability. All mallets are fitted with wood handles.

Ideal for the jewellery trade, sheet metal work and use on copper, brass and soft metals.



SQUARE BRASS MALLET



Manufactured from extruded rod these square brass mallets are fitted with wood handles. Also available with fiberglass handles, suffix FG.

Ideal for firm blows without the risk of damage to expensive components.

These mallets are not recommended for non-sparking applications. Our associate company SAFETY TOOLS LTD can quote for the appropriate Beryllium-Copper or Aluminium-Bronze tools.

Wood Handle	Fiberglass Handle	Head Size		Approx Weight
Ref No.	Ref No.	mm	mm	g
27-40500	27-40500FG	25	85	500
27-40750	27-40750FG	32	89	750
27-41000	27-41000FG	38	87	1000
27-41500	27-41500FG	38	121	1500
27-42000	27-42000FG	44	114	2000
27-42500	27-42500FG	44	146	2500
27-43000	27-43000FG	50	135	3000
27-43500	27-43500FG	50	155	3500
27-44000	27-44000FG	50	178	4000
27-44500	27-44500FG	63	124	4500
27-45000	27-45000FG	63	140	5000
27-45500	27-45500FG	63	156	5500
27-46000	27-46000FG	63	172	6000
27-47000	27-47000FG	63	194	7000
27-47500	27-47500FG	63	223	7500

Ref No.	Size	Approx Weight	Face Diameter		Head Length Approx	
Ref No.		g	inch	mm	inch	mm
02-108	0	90	1	25	2	50
02-110	1	130	1.1/4	32	2.1/2	63
02-112	2	190	1.1/2	38	3	75
02-114	3	250	1.3/4	44	3.1/4	81
02-116	4	340	2	50	3.1/2	89
02-120	5	570	2.1/2	63	4	102
02-122	6	680	2.3/4	70	4.1/2	114
02-123	7	790	2.3/4	70	4.3/4	120
02-124	8	900	3	76	5	127
02-125	9	1020	3	76	5.1/2	140
02-128	10	1250	3.1/2	89	5.1/2	140