

Quick coupling socket KD4-N-9

Part number: 531641

FESTO



Data sheet

Feature	Value
Nominal size	7.4 mm
Short type code	KD4
Operating pressure complete temperature range	-0.95 bar ... 12 bar
Standard nominal flow rate	1008 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
Ambient temperature	-10 °C ... 60 °C
Product weight	57 g
Pneumatic connection, port 1	N-9
Note on materials	RoHS-compliant