

## Han B Hood Side Entry LC 2 Levers PG 16



Part number	09 30 010 1531
Specification	Han B Hood Side Entry LC 2 Levers PG 16
HARTING eCatalogue	<a href="https://b2b.harting.com/09300101531">https://b2b.harting.com/09300101531</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> B
Type of hood/housing	Hoods
Type	Low construction

### Version

Locking type	Double locking lever (on the hood)
Han-Easy Lock <sup>®</sup>	Yes
Size	10 B
Version	Side entry
Cable entry	1x Pg 16
Field of application	Standard hoods/housings for industrial connectors

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

### Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (locking)	Polycarbonate
	Stainless steel
Colour (locking)	RAL 7037 (dust grey)
Material flammability class acc. to UL 94 (locking levers)	V-0
RoHS	compliant



Pushing Performance

## Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Approvals	DNV GL
-----------	--------

## Commercial data

Packaging size	1
Net weight	189.4 g
Country of origin	Germany
Customs tariff number	85389099