

# T cable tie



## Cable binders

Cable ties with plastic lug for directionality and mounting cables and lines.

## Application

- Plant and machine construction
- Robot construction
- Automation technology
- Vehicle construction and shipbuilding
- Rail technology
- Installation technology
- Control cabinet construction

## Material

Polyamide 6.6

- halogen-free
- silicone-free

## Note

black: good UV-resistance

## Technical data

Temperature range: -40°C up to +85°C

Flammability acc. to UL 94: V2

Part no. transparent	Part no. black	Type	Length mm	Width mm	Bundle Ø mm	Capacity N	Unit	Net EUR/100 items at a purchase of		
								up to 1000	1001 - 5000	5001 - 10000
90150	90140	T 2-20	100,0	2,5	24,0	110,0	100	o. r.	o. r.	o. r.
90151	90141	T 2-50	200,0	2,5	55,0	110,0	100	o. r.	o. r.	o. r.
90152	90142	T 3-35	140,0	3,5	36,0	200,0	100	o. r.	o. r.	o. r.
90153	90143	T 3-50	200,0	3,5	55,0	200,0	100	o. r.	o. r.	o. r.
90154	90144	T 3-75	280,0	3,5	80,0	200,0	100	o. r.	o. r.	o. r.
90157	90147	T 5-85	200,0	4,5	51,0	280,0	100	o. r.	o. r.	o. r.
90156	90146	T 5-75	280,0	4,5	76,0	280,0	100	o. r.	o. r.	o. r.
90158	90148	T 5-100	360,0	4,5	101,0	280,0	100	o. r.	o. r.	o. r.
90159	90149	T 8-100	360,0	7,5	101,0	650,0	100	o. r.	o. r.	o. r.
96491	96492	T 9-165	610,0	9,0	185,0	800,0	100	o. r.	o. r.	o. r.
97219	97223	T 9-230	762,0	9,0	236,0	800,0	100	o. r.	o. r.	o. r.

Dimensions and specifications may be changed without prior notice.

o. r. = on request