

Quick coupling plug KS2-M5-A

Part number: 531658

FESTO



Data sheet

Feature	Value
Nominal size	2.4 mm
Short type code	KS2
Operating pressure complete temperature range	-0.95 bar ... 12 bar
Standard nominal flow rate	126 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
Ambient temperature	-10 °C ... 80 °C
Nominal torque	0.85 Nm
Tolerance for nominal tightening torque	± 15%
Product weight	5 g
Pneumatic connection, port 1	Male thread M5
Note on materials	RoHS-compliant