



### Main

Range	Thalassa
Product name	Thalassa TBS
Device application	Multi-purpose
Category	Industrial box
Height	5.43 in (138 mm)
Maximum Width	3.66 in (93 mm)
Depth	2.83 in (72 mm)
Internal height	4.92 in (125 mm)
Internal width	3.15 in (80 mm)
Internal depth	2.56 in (65 mm)
Enclosure mounting	Wall mounted
Device composition	1 body 1 cover 4 cover screw
Quantity per set	Set of 2
Body type	One piece moulded
Type of front cover	Low plain cover
Cover fixing	Plastic screws
Lock type	Captive screw flat outside sealed area
Removable parts	Cover by captive screws

### Complementary

Material	ABS (acrylonitrile butadiene-styrene)
Color	Grey (RAL 7035)
Standards	IEC 62208
Product certifications	TÜV
Electrical insulation class	Class II
IP degree of protection	IP66 NEMA 4.4X
IK degree of protection	IK07 conforming to IEC 62262
Glow wire resistance	1202 °F (650 °C) IEC 60695-2-11
Ambient air temperature for storage	5...104 °F (-15...40 °C)
Operating temperature	-13...140 °F (-25...60 °C)
Net Weight	0.49 lb(US) (0.22 kg)

### Ordering and shipping details

Category	80033 - ENCLOSURE SYSTEMS POLYESTER
Discount Schedule	ES1
GTIN	03606480165269
Nbr. of units in pkg.	2
Package weight(Lbs)	0.97 lb(US) (0.44 kg)
Returnability	No
Country of origin	HU

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.91 in (7.4 cm)
Package 1 width	3.66 in (9.3 cm)
Package 1 Length	5.43 in (13.8 cm)
Unit Type of Package 2	BB1
Number of Units in Package 2	2
Package 2 Weight	15.78 oz (447.25 g)
Package 2 Height	3.27 in (8.3 cm)
Package 2 width	5.63 in (14.3 cm)
Package 2 Length	7.99 in (20.3 cm)
Unit Type of Package 3	CAR
Number of Units in Package 3	58
Package 3 Weight	31.04 lb(US) (14.08 kg)
Package 3 Height	15.75 in (40 cm)
Package 3 width	15.94 in (40.5 cm)
Package 3 Length	23.82 in (60.5 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------