

## T-slot bolts



### Application:

For clamping workpieces on machine tables.

### Execution:

- Tempered
- Rolled thread
- Forged
- With milled groove guide
- M8 to M12, strength class 10.9
- M16 to M24, strength class 8.8
- DIN 787



|                                 |                  |
|---------------------------------|------------------|
| <b>Art. no.</b>                 | <b>26200 350</b> |
| <b>Brand</b>                    | AMF              |
| <b>Manufacturer Part Number</b> | 80887            |
| <b>DIN</b>                      | 787              |
| <b>Thread dimension</b>         | M12              |
| <b>Groove width</b>             | 12 mm            |
| <b>Length excluding head</b>    | 200 mm           |
| <b>Outer diameter</b>           | 11.7 mm          |
| <b>Thread length</b>            | 120 mm           |
| <b>Length of head</b>           | 18 mm            |
| <b>Head height</b>              | 7 mm             |
| <b>Gross Weight</b>             | 0.211 kg         |
| <b>Product Group</b>            | 260              |

### EAN

4020772080884