

## DICHT-BECHERBLINDNIETE



GROSSKOPF MIT GERILLTEM NIETDORN

## SEALED BLIND RIVETS

LARGE HEAD WITH GROOVED MANDREL

## RIVETS ÉTANCHES

TÊTE LARGE AVEC CLOU CANNÉLÉ



Edelstahl A2 [ 1.4301 ]  
Stainless steel A2 [ AISI 304 ]  
Acier inox A2 [ 1.4301 ]

Edelstahl C1 [ 1.4021 ]  
Stainless steel C1 [ AISI 420 ]  
Acier inox C1 [ 1.4021 ]

### Ø 3,2 mm

#### D2 = 10,0 mm

D1 = 3,2 + 0,08 / - 0,10 mm

D2 = 10,0 + / - 0,29 mm








k = - 0,9 + / - 0,3 mm

d = 1,9 mm

P ≥ 27,0 mm

L = + 1,0 / - 0,2 mm

 3,3 mm

						
3,2 x 6,0 mm	0,5 - 1,5 mm	21811 32600	2000 N	2500 N	1000	10000
3,2 x 8,0 mm	1,5 - 3,0 mm	21811 32821				
3,2 x 10,0 mm	3,0 - 5,0 mm	21811 32100				
3,2 x 12,0 mm	5,0 - 6,5 mm	21811 32120				

### Ø 4,0 mm

#### D2 = 12,0 mm

D1 = 4,0 + 0,08 / - 0,10 mm

D2 = 12,0 + / - 0,35 mm








k = - 1,1 + / - 0,3 mm

d = 2,3 mm

P ≥ 27,0 mm

L = + 1,0 / - 0,2 mm

 4,1 mm

						
4,0 x 6,0 mm	0,5 - 1,5 mm	21811 40600	3000 N	4000 N	500	5000
4,0 x 8,0 mm	1,5 - 3,0 mm	21811 40800				
4,0 x 10,0 mm	3,0 - 5,0 mm	21811 40100				
4,0 x 12,0 mm	5,0 - 6,5 mm	21811 40120				
4,0 x 16,0 mm	6,5 - 10,5 mm	21811 40160				

### Ø 4,8 mm

#### D2 = 14,0 mm

D1 = 4,8 + 0,08 / - 0,10 mm

D2 = 14,0 + / - 0,35 mm








k = - 1,3 + / - 0,3 mm

d = 2,9 mm

P ≥ 27,0 mm

L = + 1,0 / - 0,2 mm

 4,9 mm

						
4,8 x 8,0 mm	0,5 - 3,0 mm	21811 48800	4500 N	5500 N	250	2500
4,8 x 10,0 mm	3,0 - 5,0 mm	21811 48100				
4,8 x 12,0 mm	5,0 - 6,5 mm	21811 48120				
4,8 x 16,0 mm	6,5 - 10,5 mm	21811 48160				
4,8 x 20,0 mm	10,5 - 14,0 mm	21811 48200				