

Product Specification PDF

| | |
|-------------------|------------------------------------|
| Date | Correct as of 12th May 2020 |
| Brand | C.K |
| Product | T1642 |
| Description | Electronic Service Case |
| Barcode | 5013969984910 |
| Commodity code | 8206000000 |
| Country of origin | DE |



Features & Benefits

~ Professional ABS tool case with aluminum frame ~ 2 high quality press button locks, lockable, additional 3-digit combination lock ~ Bottom tray 59 mm high, with variable dividers ~ Bottom tray lid, flush fitting, 14 compartments ~ Tool board double sided, 32 tool compartments and elastic band for 12 parts, detachable ~ 1 fixed Din A4 document compartment with additional compartments for CD's, mobile phone, business cards and pen ~ Inner dimensions: 460 x 160 x 310 mm Case contents: ~ Precision Side Cutter, 115 mm ~ Precision Snipe Nose Pliers, 145 mm ~ Radio Tweezers, 155 mm ~ Inspection Mirror, telescopic, 32 mm Ø ~ Precision Screwdriver 2,5 x 60 mm ~ Precision Wire Stripper 0,25 ~ 0,80 mm Ø ~ VDE Snipe Nose Pliers, straight, 200 mm ~ VDE Combination Pliers, 185 mm ~ VDE Side Cutter (Combicutter), 160 mm ~ VDE Screwdrivers, slotted: 3x100 / 4x100 / 5,5x125 / 6,5x150 mm ~ VDE Screwdrivers: PZD: 0x60 / 1x80 mm ~ VDE Screwdrivers: PH: 0x60 / 2 x 100 mm ~ Mains tester 140 mm ~ Electrician's knife ~ Switch key wrench ~ Automatic Wire Stripping Pliers, Jokari Super 4 ~ 0,2-6,0 mm² ~ Jokari Cable Knife 28H 8-28 mm ~ Electrician's Scissors ~ Multi-purpose Snips ~ Hexagon Key Set 1,5-7 mm ~ Nut Spinners: 5,5 / 7 / 8 & 10 mm

Applicable Standards

Health & Safety

None applicable

Warranty

C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through normal wear and tear or resulting from inappropriate use, is not covered.

Product Weights and Measures

| | Product only | Product & primary packaging | Secondary packaging | Transit packaging |
|-----------------------|--------------|-----------------------------|---------------------|-------------------|
| Item Quantity | 1 | 1 | 0 | 1 |
| Width mm | 170 | 0 | 0 | 175 |
| Depth mm | 480 | 0 | 0 | 495 |
| Height mm | 360 | 0 | 0 | 393 |
| Weight | 6350 | 6350 | 0 | 7.1 |
| Packaging Information | Card use | 0 | 0 | Case |
| | Card gms | 0 | 0 | 787.5 |
| | Plastic use | 0 | 0 | - |
| | Plastic gms | 0 | 0 | 0 |
| | Metal use | - | 0 | - |
| | Metal gms | 0 | 0 | 0 |
| | Timber use | - | 0 | - |
| | Timber gms | 0 | 0 | 0 |