



**RMMER 11/24 AC/DC OUTPUT RELAY**

IN: 24 VAC/DC - OUT: 250 VAC/DC / 5 A

1 relay; 1 NC contact  
24 V AC/DC  
Screw terminals

[Link to Product](#)**Illustration**



Product may differ from Image

### Utilization category

AC-1	5 A (24/110/230 V AC)
AC-15	3 A (24/110/230 V AC)
DC-13	1.5 A (24 V DC); 0.3 A (110 V DC); 0.15 A (230 V DC)

### Input

Connection voltage - current	24 VAC/DC (19.2...30 VAC/DC) - 15mA
LED display	LED (yellow)

### General data

Mech./ elect. life	100.000.000 switching cycles/load dependent
Test isolation voltage	1.5 kV
Mounting method	DIN-rail mountable TH35 or G32 (EN 60715)
Temperature range	-20...+60 °C
Dimensions H x W x D	56x12x65 mm

### Output

Switching voltage	max. 125 V AC/DC
Switching current per output	max. 1 A
Min. load current	1 mA
Power rating (voltage dependent)	max. 60 VA/30 W
Switching frequency	max. 15 Hz
Contact material	Pd Ni-Au Rh
Energize/release/contact bounce time	10/10/1 ms

### Commercial data

country of origin	CZ
customs tariff number	85364900
minimum order quantity	1