

Quick coupling socket NPHS-D6-M-G14

FESTO

Part number: 8059275



Data sheet

Feature	Value
Nominal width	8.2 mm
Type code	NPHS NPHS
Operating pressure for entire temperature range	-0.95 bar ... 20 bar
Standard nominal flow rate	1833 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:] Compressed air as per ISO 8573-1:2010 [7:-:]
Information on operating and pilot media	Operation with oil lubrication possible Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress 1 - Low corrosion stress
Ambient temperature	-20 °C ... 80 °C
Nominal tightening torque	7 Nm
Tolerance for nominal tightening torque	± 20% ± 20%
Product weight	173 g
Pneumatic connection 1	External thread G1/4 External thread G1/4
Note on materials	RoHS-compliant RoHS-compliant