

TECHNICAL DATASHEET


Update : 25/02/2019

OGIVE-SHAPED CARBIDE MILLING BIT ROUNDED HEAD - FORM F



Description

For use, please refer to the table on page 109



Characteristics

Ref.	EAN	Tail diameter mm	Shape of head	Total length	Teeth	Head diameter	Scope	Capacity length mm
847258	3660338086168	3	Model F	38	Crossed	3	Universal	13
847259	3660338086175	6	Model F	50	Crossed	6	Universal	16
847260	3660338086182	6	Model F	65	Crossed	9,5	Universal	19
847261	3660338086199	6	Model F	70	Crossed	12,7	Universal	25
863176	3660338177873	3	Model F	45	Crossed	6	Universal	13
863177	3660338177880	6	Model F	70	Crossed	16	Universal	25
863178	3660338177897	6	Model F	65	Negative	9,5	Rough outline	19
863179	3660338177903	6	Model F	70	Negative	12,7	Rough outline	25
863180	3660338177910	6	Model F	65	Steel	9,5	Rough outline	19
863181	3660338177927	6	Model F	70	Steel	12,7	Rough outline	25
863182	3660338177934	6	Model F	65	Stainless steel	9,5	Rough outline	19
863183	3660338177941	6	Model F	70	Stainless steel	12,7	Rough outline	25
863184	3660338177958	3	Model F	38	Simple	3	Finish	13
863185	3660338177965	3	Model F	45	Simple	6	Finish	13
863186	3660338177972	6	Model F	50	Simple	6	Finish	16
863187	3660338177989	6	Model F	65	Simple	9,5	Finish	19
863188	3660338177996	6	Model F	70	Simple	12,7	Finish	25
863189	3660338178009	6	Model F	65	Diamond	9,5	Finish	19
863190	3660338178016	6	Model F	70	Diamond	12,7	Finish	25
863191	3660338178023	6	Model F	50	Alu	6	Alu	16
863192	3660338178030	6	Model F	65	Alu	9,5	Alu	19
863193	3660338178047	6	Model F	70	Alu	12,7	Alu	25